

Cardinal Circuit

Stocking Dealer of Electronics Assembly Equipment

www.cardinalcircuit.com

Brand New Electrovert Electra Wave Solder Spare Parts

The list below is in Numerical order by Electrovert Part Numbers. All parts on the list are Brand New parts that have never been used.

| PART NUMBER | DESCRIPTION |
|-----------------|--|
| 64425 | Lamp 20W |
| 6-1909-028-13-1 | Pre-Heater Cable |
| 6-1909-028-13-1 | Pre-Heater Cable (Rebuilt) |
| 2-5001-402-01-0 | Lower Pre-heat Blower Motors |
| 2-5001-444-00-0 | Motor, Solder Pump |
| 2-5006-145-00-0 | Contactora, Mercury, 3 POS, 24 V DC Coil, 30 A |
| 2-5008-257-00-0 | Switch, Liquid Level .55SG, Polypro |
| 2-5008-517-00-0 | Switch, Limit, SPDT-BD 2NO, 2NC, Side Rotary |
| 2-5008-518-00-0 | Switch, Limit, SPDT INC, 1C, 1BLNK, Roll Plung |
| 2-5008-524-00-0 | Exhaust Sensor |
| 2-5008-542-00-0 | Solder Level Sensor |
| 2-5012-142-01-0 | Blub, XELOGEN, 12V,20W 2 Pin |
| 2-5020-378-00-0 | FUSE, FNQ, 30A .41X1.5 |
| 2-5020-383-00-0 | FUSE, FNQ, 25A .41X1.5 |
| 2-5026-070-00-0 | Thermocouple, Type K SS304/Fiberglass |
| 2-5026-165-00-0 | Thermocouple, Type K Inconel 600/Fiberglass |
| 2-5026-167-00-0 | Thermocouple, Type K SS316/Fiberglass,4.5 |
| 2-5030-010 | Position Transducer |
| 2-5030-050-00-0 | Position Transducer |
| 2-5065-120-01-0 | Keyboard |
| 2-5999-337-00-0 | Filter, Fan Inlet Assy |
| 2-5999-439-01-0 | Pre-heat blower Current Sense Relay |

| PART NUMBER | DESCRIPTION |
|--------------------|--|
| 2-5999-470-00-0 | Wave height sensor and receiver |
| 2-6001-071-00-0 | SPROCKET,DRIVE,18T,.75ID KEYWAY |
| 2-6002-007-00-0 | Chain, Master link, 25 Pitch |
| 2-6002-011-00-0 | Chain, Master link, 35 Pitch |
| 2-6002-060-01-0 | Chain, ASI Spring Clip, ASA 40 to 2 Pitch |
| 2-6002-060-01-0 | finger clip |
| 2-6002-068-03-0 | Chain, Master link, 40 Pitch |
| 2-6003-059-00-0 | Belt, Timing 3/8,0.142, X .50 X 30.0 POLY |
| 2-6004-572-00-0 | BEARING,S ROW BALL, .750 X 1.750 X .750,SLD |
| 2-6004-580-00-0 | Solder Pump Bearing, s Row Ball 20mm X 47MM X 14MM 1 SHD |
| 2-6010-009-00-0 | Ring, External, Retaining 0.5 OD, Basic STL |
| 2-6010-107-00-0 | Ring, External, Retaining 0.718 OD, Basic SS |
| 2-6010-108-00-0 | Ring, External, Retaining 1.875 OD, Basic SS |
| 2-6049-338-00-0 | Switch, Level, LVS001 |
| 2-6049-340-00-0 | Photocell, Incoming |
| 2-7999-278-00-0 | Curtain, Solder,Wave |
| 2-8003-468-00-0 | N2- (Quick Connect) Female for Pot connections |
| 2-8010-082-00-0 | Fitting, Coupling M Body 1/2 FNPT |
| 2-8010-210-00-0 | Fitting, Coupling F Body 3/4 ID BRB |
| 2-8025-362-00-0 | N2 - Hose Teflon/SS for Solder Pot |
| 2-9304-066-00-0 | Adhesive, Lubricant High Temperature (AP Grease) |
| 3-0053-147-01-6 | Brush, Finger Cleaner 35X209MM, Nylon |
| 3-0053-148-01-6 | Brush Finger Cleaner |
| 3-0058-178-03-6 | Brush, Shaft, Rotary Chip, Titanium |
| 3-0132-241-01-4 | Curtain, Solder, Fluxer Side, 320 MM, Silicone |
| 3-0172-186-01-6 | Nitrogen tube Pot N2 diffuser |
| 3-0253-197-01-6 | Light Assembly (New type) |

| PART NUMBER | DESCRIPTION |
|--------------------|--|
| 3-0257-192-14-3 | Finger, L, Groove Titanium, 2.4 MM |
| 3-0257-242-01-3 | Finger, V, Groove Titanium, 2.4 MM |
| 3-0909-258-01-6 | SPROCKET, DUAL, TENSIONER, 17T, 26.7MM ID |
| 3-0909-267-01-6 | SPROCKET, DRIVE, DUAL, 17T, .75ID, KEY, SET |
| 3-1670-113-10-6 | Solder level Sensor Cable |
| 3-956-435-02-6 | Pot Screw Jack (used) |
| 3-956-435--02-6 | Pot Screw Jack |
| 72.205.1053.0 | Wieland Connector Insert (Pre- heat cable) |
| 72.215.1053.0 | Wieland Connector Insert (Pre- heat cable) |
| | Documentation CD |
| | Bottom Covers (from pallet return tunnel) |